| Description  | Kluge & Fielitz GmbH  |
|--|---|
| Description  | Rehabilitation Cleaning and Disinfection Systems                          |
| Product:   | Bed washing system type KF 900  |
| Certified Clean Care   |   |
| Features   |   |
| Suitable for   | Hospital beds, wheelchairs, walkers, AD mattresses, etc.                  |
| Capacity   | for example 1 hospital bed, 3 wheelchairs                                 |
| Cleaning programs  | Duration 8,10 or 12 min.  |
| Disinfection programs  | 2 (Duration 15 minutes)   |
| Custom   | yes   |
| Washing programs possible available with condensation drying | Serie   |
| Washing temperature  | Adjustable up to 60 degrees °C  |
| mobile   | yes   |
| Water consumption  | 35-45 litres  |
| Tap water  | min. 2 bar  |
| Supply or waste water connection                             | Faucet 1/2" with external thread 3/4" or drain connection 1/2"            |
| Electrical connection conditions                             | Socket 400 Volt / 32 A or 63Ass   |
| Energy consumption   | 2.8 kW per wash cycle   |
| Service  |   |
| Touch panel with control display                             | yes   |
| Viewing Work Information                                     | yes   |
| Technical displays selectable                                | yes   |
| Number of washing cycles (touch panel display)               | yes   |
| USB interface for information                                | yes   |
| Program display  | yes   |
| Safety Emergency stop switch in the (Hand Area)              | voc   |
| During operation, open door-automatic stop                   | yes<br>yes  |
| Canister detergent empty - shut-off / display                | yes   |
| Noise level in dB(A)   | 62  |
| Disinfection test possible for customers                     | yes   |
| Dimensions   | )   |
| Dimensions LxWxH   | 2500 mm x 2110 mm x 2500 mm (with technical part right or left)           |
| Dimensions LxWxH (in the washing chamber)                    | 2450 mm x 1430 mm x 1950 mm   |
| Dimensions selectable / adjust                               | yes   |
| Delivery in modules / assembly at the customer's             | yes   |
| site   | voc   |
| put in a pit   | WA inserted into pit - 0 mm; 170 mm without wheels; 270 mm with wheels    |
| Entrance height  | WA inserted into pit - 0 min, 170 min without wheels, 270 min with wheels |
| Weight   | 1400kg (depending on equipment)   |
| Maintenance  |   |
| Lifetime at least  | 8-10 years  |
| Number of washing cycles / year                              | Up to 3,000   |
| Maintenance information is displayed in advance              | yes   |
| Filter easy to clean - without tools                         | yes<br>Stainless steel  |
| Materials for filters  | Stainless steel   |
| Program changes - at the customer's request  Error display   | yes Ves (indicator light / honking sound)                                 |
| Other auxiliary devices                                      | Yes (indicator light / honking sound)                                     |
| Trolley  | yes   |
| Transport trolleys according to customer                     | yes   |
| requirements Validated fogging disinfection                  | for foam and sensitive materials - on customer request                    |
| Standards  | Total and solishing matchais - on customer request                        |
| CE, Medical Device Class II a                                | 93/42/EEC; MDR; ISO 15883; DIN 13485                                      |
| MOT  | yes   |
| Warranty   | <u></u>   |
| Years (extension possible)                                   | 1   |
| 1 /  | ı   |